

High Frequency Inverter X-ray System



PT. Permana Putra Mandiri
Medical Equipment Supplies and Services
Jl. Taman Mini Indonesia Indah (TMII) Pintu II atas No. 43 Cipayung, Jakarta Timur - Indonesia
Phone : 021 841 5976, Fax: 021 840 7865
Email: info@ptppm.id, marketing@alatkedokteran.id
www.ptppm.id | www.alatkedokteran.id



WSR-40

High Frequency Inverter X-ray System



Can reduce shooting time about 50% than general method when WSR-40 system films human body by high frequency inverter method and because control console is small and light, is possible by wall tapestry and Radiographic is available by remote control switch conveniently that user films. And have A.P. R function to basis.

SPECIFICATIONS

Component	Item	WSR-40
Consol& Generator	kVp Range	40~125kV
	mA Range	50mA ~ 500mA
	mAs Range	0.5mAs ~ 600mAs
	Time Range	0.01 ~ 6sec
	Sys-Self Diagnosis	LED code display
	A.P. R Output Frequency	576kinds 60KHZ
Tube unit	Tube Voltage Anode Heat	500mA/125kvp 140,000HU
Tube Stand	U/D mov. dis L/D mov. dis Revo. angle	Approx. 1300mm (680 to 1980mm) Approx. 1480mm Rail 2400mm 360°
Table	L/R mov. dis	±350mm (2,000L x 728W x 710H)
Collimator	Lighting	More than 160 Lux at SID 100cm
H.T cable	kvp Range	Max. 150kVp
Option	Bucky Stand Ceiling	
	6way- table	

PT. Permana Putra Mandiri
Medical Equipment Supplies and Services
Jl. Taman Mini Indonesia Indah (TMII) Pintu II atas No. 43 Cipayung, Jakarta Timur - Indonesia
Phone : 021 841 5976, Fax: 021 840 7865
Email: info@ptppm.id, marketing@alatkedokteran.id
www.ptppm.id | www.alatkedokteran.id

